

CapSURE™ – LP

100% Polyester Sealed Edge Cleanroom Wiper

CapSURE™-LP is a sealed edge cleanroom laundered wiper that has been specially engineered for superior surface cleaning ability. A patent pending surface treatment allows the wiper to capture and retain particulate contamination,

resulting in more efficient cleaning and reduced likelihood of cross contamination of critical surfaces. CapSURE™-LP has the high level of cleanliness and abrasion resistance required for ISO Class 3 and above environments and applications requiring critical control of contaminants



Key Attributes

- Patent pending surface treatment captures and retains particulate contamination
- 100% continuous filament polyester knit
- Sealed edge for reduced fiber contamination
- Laundered and packaged in Berkshire's ISO Class 4 cleanroom

Benefits

- Minimal particles, fibers, ions and extractables.
- Airborne particle release 80% lower than competitive particle attraction wipers
- Captures 42 times more particles than competitive (untreated) wipers
- Retains 93% of particles captured
- Unique knit construction yields high abrasion resistance
- Immediate adsorption of liquids for efficient spill clean-up
- Autoclavable

Environmental

- Complies with RoHS 2002/05 and REACH requirements

Other Class 3 and above wipers

- MicroSeal SuperSorb®
- UltraSeal® 3000
- MicroSeal® 1200
- ValuSeal® LP
- ValuSeal® HA
- ValuSeal® 1500

Applications

- Designed for use in ISO Class 3 and higher cleanroom environments
- Designed for the highest level of contamination control in critical processing applications
- Oxidation, Metallization, CVD or Photolithography processes
- Chamber cleaning and CMP processing
- Stencil and other print roll cleaning applications
- Steam autoclavable for aseptic applications
- Cleaning of medical device products
- Applying and removing cleaning and disinfecting solutions

Value Pack Option

The value pack option provides the same great performance in a more economical bulk packaging format.

www.berkshire.com

Contact: Tel 1 800 242 7000 / 1 413 528 2602
info@berkshire.com

Americas	Tel 1 413 528 2602	Fax 1 413 528 2614	usa@berkshire.com
Europe	Tel 44 (0) 870 757 2877	Fax 44 (0) 870 757 2878	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	Fax 65 6252 4312	enquiries@berkshire.com.sg
Japan	Tel 81 45 477 4481	Fax 81 45 477 4484	master@berkshire.co.jp

Technical Data:

Attribute		Units	Value	Test Method
Basis Weight		g/m ²	143	TAPPI T-410
Caliper		µm	411	TAPPI T-411
Fibers	≥100µm	fibers/cm ²	0.06	TEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.2
Liquid Particles	≥0.5µm	x10 ⁹ /cm ²	0.52	TEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.2
Airborne Particles	≥0.5µm	particles/m ³ /ft ³	51	TEST-RP-CC-003.2
Sorbency	Capacity	mL/m ²	404	TEST-RP.CC004.3, Sec 8.1 modified / Sec 8.2 modified
	Efficiency	mL/g	2.8	
	Rate	seconds	1	
Non-Volatile Residue	DI Water	g/m ²	0.011	TEST-RP.CC004.3, Sec 7.1.2
	IPA	g/m ²	0.011	
Ions	Na ⁺	ppm	0.054	TEST-RP.CC004.3, Sec 7.2.2
	K ⁺	ppm	0.012	
	Ca ⁺⁺	ppm	0.042	
	Mg ⁺⁺	ppm	0.011	
	Cl ⁻	ppm	0.10	

Notes:

- All values are statistical averages
- Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

Order Information:

Product	Number	Size	Shts/pk	Pks/cs	Style
CapSURE™-LP	CPSLP.0909.8	9x9" (23x23cm)	150	8	Stacked
CapSURE™-LP	CPSLP.0909B.8	9x9" (23x23cm)	150	8	Value Pack
CapSURE™-LP	CPSLP.1212.14	12x12" (30x30cm)	75	14	Stacked
CapSURE™-LP	CPSLP.1212B.14	12x12" (30x30cm)	75	14	Value Pack

For more information on our other contamination control products or technical consultation, please contact your Berkshire Sales Representative or e-mail: info@berkshire.com

Other Berkshire products

For information on our other products, please click on the relevant text.



Wipers




Mop Systems




Face Masks



Glove Liners



Documentation Systems



Swabs