

Smart Tweezers™

LCR Meter and Component Identifier in a Pair of Tweezers

An Efficient and Convenient Way to Test SMD Components

- Built-in high-precision LCR probe
- Convenient one-hand operation
- · Ideal for Surface Mount Devices
- Automated component identification
- Automated test range selection
- Manual C, R, L, Z and ESR modes
- Adjustable test signal levels
- Swiss-made precise test leads
- Diode Polarity/Short Testing
- Secondary D, Q and ESR parameters
- · Portable and ergonomic design
- Built-in Li-Ion battery



Smart Tweezers™ greatly simplifies testing and troubleshooting process.





Resistance, capacitance and inductance can be measured with automatic selection of the test parameters and range.

Smart Tweezers™ is a handheld LCR meter of a new concept. It provides a perfect solution for testing and identification of Surface Mount Devices as well as troubleshooting of complex electronic systems.

Its unique mechanical and electronic design combines a pair of precise gold-plated tweezers and a digital LCR meter in compact, lightweight, battery powered instrument. The probe is able to measure resistance, capacitance, inductance with high accuracy and automatic component identification

Testing Surface Mount Devices

Surface mount devices are usually tiny and without wire leads, making it more difficult to test and identify SMD than conventional components.

Smart Tweezers™ gives users an easy way to sort and evaluate loose components and to perform on-board measurements and debugging.

Precise leads produced by IDEAL-TEK S.A., Switzerland reliably contact even the smallest SMD components and take measurements from already mounted devices. The probe can also be used to test conventional components with wire leads too short to insert into the test terminals.

Automated Measurements

Do measurements faster with Smart Tweezers™ using the automatic component identification function eliminating unnecessary trial and error time.

Smart Tweezers™ automatically specifies L, C, or R with parallel and series mode and selects a proper measurement range and test frequency for high accuracy measurements. The unit displays component type and more detailed component analysis such as Z and ESR.

Lightweight and Ergonomic

The integrated measurement head allow the operator to use one hand and focus attention on the tested component and on the job at hand. Sorting, testing and troubleshooting become more efficient and cost effective.

4-wire shielded Smart Tweezers™ handles assure low capacitance and resistance offset during measurements.

Wide Spectrum of Additional Functions

- Smart Tweezers[™] LCR meter allows you to test various component types, including secondary components of Dissipation Factor (D), Quality Factor (Q). This handheld also includes other functions that result in a more detailed component analysis.
- The built-in Equivalent Series Resistance (ESR) mode helps you better understand the inherent resistance behavior typically found in capacitors across selected frequencies.
- In its DIODE mode Smart
 Tweezers™ tests diode polarity
 and indicates if it is short.
- Smart Tweezers[™] has a continuity detector. Variable beeper sounds for resistance reading below set thresholds. Additionally, this function helps to locate shorted conductors (e.g. on a PCB).
- In manual modes Smart
 Tweezers™ measures a specific
 circuit parameter L, C, R, Z or
 ESR. Manual modes also improves
 component type identification for
 in-circuit tests.
- Variable test signal output from 0.25 to 1.0 Vrms allows to improve test precision in different situation e.g. for in-circuit measurement and loose leaded ceramic capacitors.
- Visible and audible tolerance mode allows to perform component sorting.
- Math null function allows to store a pre-measured offset and improve measurement precision.



Technical Specifications

AC test mode Test frequency:

Test frequency accuracy:

Test signal level:

Source impedance:

1 kHz, 10 kHz, 120Hz,100 Hz

50 PPM (0.005%)

0.25/0.5/1.0 +/- 5% Vrms Sine wave

 $62.5\Omega/1k\Omega/16k\Omega + /-1%$

Measurement Ranges

Resistance R:

Capacitance C:

Inductance L:

Quality factor Q:

Dissipation factor D:

0.5 uH to 999 mH 0.001 to 1000

 $0.05~\Omega$ to $9.9~M\Omega$

0.5 pF to 4999 µF

0.001 to 1000

Physical Specifications

Size

Weight

Operating temperature:

Battery Type:

Battery Life (continuous)

14.0 x 2.5 x 3.0 cm (3.94 x 0.9 x 1.5 in)

53 grams (0.11 lb)

0°C to 50°C

3.7V LiPO rechargeable 150mAH

80 hours, 2 hours charging cycle

Accuracy Specifications

Resistance, impedance.

Range	Resolution	100 Hz	1 kHz	10kHz
1 R	0.001R	0.7% + 50	0.7% + 50	0.7% + 50
10 R	0.01R	0.7% + 8	0.7% + 8	0.7% + 8
100 R	0.01R	0.2% + 3	0.2% + 3	0.2% + 3
1000	0.1R	0.2% + 3	0.2% + 3	0.2% + 3
10 kO	0.001K	0.2% + 3	0.2% + 3	0.2% + 3
100 kO	0.01K	0.5% + 5	0.5% + 5	0.5% + 5
1000 kO	0.1K	0.5% + 5	0.5% + 5	0.5% + 5
10 MO	0.001K	2.0% + 8	2.0% + 8	5.0% + 8

Accuracy for the ranges 1 R \sim 100 R is specified after subtract of the offset resistance.

Capacitance

Range	Resolution	100 Hz	120 Hz	1 kHz	10 kHz
10 mF	0.001 mF	2.0% + 8	2.0% + 8	NA	NA
1000 μF	0.1 μF	0.5% + 5	0.5% + 5	NA	NA
100 μF	0.01 μF	0.3% + 3	0.3% + 3	0.5% + 5	NA
10 μF	0.001 μF	0.2% + 3	0.2% + 3	0.2% + 3	0.5% + 5
1 μF	0.1 nF	0.2% + 3	0.2% + 3	0.2% + 3	0.2% + 3
100 nF	0.01 nF	0.2% + 3	0.2% + 3	0.2% + 3	0.5% + 3
10 nF	0.001 nF	0.5% + 5	0.5% + 5	0.2% + 3	0.5% + 3
1000 pF1	0.1 pF	NA	NA	0.5% + 5	0.5% + 3
100 pF1	0.01 pF	NA	NA	0.5% + 10	0.8% + 20
10 pF1	0.001 pF	NA	NA	NA	1.0% + 50

Accuracy for the ranges of 10 pF~1000 pF iS specified after subtract of the stray capacitances for test leads.

Inductance

Range	Resolution	100 Hz	1 kHz	10 kHz
10 μH	0.001 μΗ	NA	NA	1.0% + 5
100 μH	0.01µH	NA	1.0% + 5	0.7% + 3
1 mH	0.1 μΗ	0.7% + 10	0.5% + 3	0.5% + 3
10 mH	0.001 mH	0.5% + 3	0.2% + 3	0.5% + 3
100 mH	0.01 mH	0.5% + 3	0.2% + 3	NA
1 H	0.1 mH	0.2% + 3	NA	NA

Advance Devices, Inc.

RPO Harding, PO Box 32043, Richmond Hill, ON L4C9S3 Canada

Phone: +1-800-453-5315 **Fax**: +1-416-352-5400

Web: www.advancedevices.com