

CapSure® – LP Edge

Bordered Sealed Edge Cleanroom Laundered Wiper 100% Polyester Knit

CapSure®–LP Edge is a 4-side sealed edge cleanroom laundered wiper that has been specially engineered for superior surface cleaning ability. A patented (#8,431,497) surface treatment allows the wiper to capture and retain particulate contamination, resulting in more efficient

cleaning and reduced likelihood of cross contamination of critical surfaces. CapSure®–LP Edge has the high level of cleanliness and abrasion resistance required for ISO Class 3 and above environments and applications requiring critical control of contaminants.



Key Attributes

- Patented surface treatment captures and retains particulate contamination, Patent #8,431,497
- 100% continuous filament polyester knit
- 4-side sealed border
- Laundered and packaged in Berkshire's ISO Class 4 cleanroom

Benefits

- Critically low particles, fibers and extractables
- 4-side border sealed edges increase durability and minimize fiber and particle release during use
- Airborne particle release 80% lower than competitive particle attraction wipers
- Captures 42 times more particles than competitive (untreated) wipers
- Retains 93% of particles captured
- Excellent combination of cleanliness, absorbency and abrasion resistance
- Immediate adsorption of liquids for efficient spill clean-up
- Steam autoclavable for use in aseptic environments

Applications

- Designed for use in ISO Class 3 and higher cleanroom environments
- Designed for the highest level of contamination control in critical processing applications
- Oxidation, Metallization, CVD or Photolithography processes
- Chamber cleaning and CMP processing
- Stencil and other print roll cleaning applications
- Steam autoclavable for aseptic applications
- Cleaning of medical device products
- Applying and removing cleaning and disinfecting solutions

Other Class 3 and above wipers

- MicroSeal SuperSorb®
- UltraSeal® 3000
- MicroSeal® 1200
- ValuSeal® LP
- ValuSeal® HA
- ValuSeal® 1500

Value Pack Option

The value pack option provides the same great performance in a more economical bulk packaging format.

www.berkshire.com

Contact: Tel 1 800 242 7000 / 1 413 528 2602
info@berkshire.com

Americas	Tel 1 413 528 2602	Fax 1 413 528 2614	info@berkshire.com
Europe	Tel 44 (0) 870 757 2877	Fax 44 (0) 870 757 2878	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	Fax 65 6252 4312	enquiries@berkshire.com.sg
Japan	Tel 81 3 5827 2380	Fax 81 3 5827 2382	master@berkshire.co.jp

Technical Data:

Attribute		Units	Value	Test Method
Basis Weight		g/m ²	141	TAPPI T-410
Caliper		μm	424	TAPPI T-411
Fibers	≥100μm	fibers/cm ²	0.026	IEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.2
Liquid Particles	≥0.5μm	x10 ⁹ /cm ²	0.30	IEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.1
Sorbency	Capacity	mL/m ²	390	IEST-RP.CC004.3, Sec 8.1 modified / Sec 8.2 modified
	Efficiency	mL/g	2.8	
	Rate	seconds	1	
Non-Volatile Residue	DI Water	g/m ²	0.0025	IEST-RP.CC004.3, Sec 7.1.2
	IPA	g/m ²	0.0085	
Ions	Na ⁺	ppm	0.12	IEST-RP.CC004.3, Sec 7.2.2
	K ⁺	ppm	0.015	
	Ca ⁺⁺	ppm	0.027	
	Mg ⁺⁺	ppm	0.0087	
	Cl ⁻	ppm	0.11	

Notes:

- Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.
- Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

Order Information:

Product	Number	Size	Shts/pk	Pks/cs	Style
CapSure®-LP Edge	CPLPE.0909.8	9x9" (23x23cm)	150	8	Stacked
CapSure®-LP Edge	CPLPE.0909B.8	9x9" (23x23cm)	150	8	Value Pack

For more information on our other contamination control products or technical consultation, please contact your Berkshire Sales Representative or e-mail: info@berkshire.com

Other Berkshire products

For information on our other products, please click on the relevant text.



[Wipers](#)



[Glove Liners](#)



[Mop Systems](#)



[Documentation Systems](#)



[Face Masks](#)



[Swabs](#)